

## NATRIX

### Natrix

- General purpose all-metal hose
- Commonly used in high temperature vacuum or general purpose applications where permeation is undesirable.

CoreDux base hose range									
Nominal Hose Size [in. (mm)]	Hose material	Braid material	Hose Inside dia. [in. (mm)]	Hose outside dia. [in. (mm)]	Minimum centre line bend radius		Working pressure at 70°F (20°C) [psig (bar)]	Minimum Burst Pressure at 70°F (20°C) [psig (bar)]	Temp. Range [°F (°C)]
					Static [in. (mm)]	Dynami c [in. (mm)]			
1/4" DN006	316L SS	304 SS	0,24 (6,2)	0,45 (11,4)	0,91 (23)	4,33 (110)	2030 (140)	8120 (560)	-325 to 800 (-200 to 426)
3/8" DN010	316L SS	304 SS	0,41 (10,4)	0,70 (17,8)	1,20 (30,5)	5,91 (150)	1470 (101)	5880 (404)	-325 to 800 (-200 to 426)
1/2" DN012	316L SS	304 SS	0,49 (12,4)	0,80 (20,2)	1,50 (38,1)	6,50 (165)	1160 (80)	4640 (320)	-325 to 800 (-200 to 426)
3/4" DN020	316L SS	304 SS	0,78 (19,9)	1,18 (29,9)	1,50 (38)	6,66 (169)	860 (59,2)	3500 (241)	-325 to 800 (-200 to 426)
1" DN025	316L SS	304 SS	0,98 (24,9)	1,43 (36,4)	1,77 (45)	7,68 (195)	680 (46,8)	2680 (184)	-325 to 800 (-200 to 426)

### Compliance

- EN ISO 9001
- EN ISO 10380 / ASME 31.3

### Cleanliness

- Standard deliveries: White room
- Vacuum, Ultra high purity: possible upon request

### Packaging

- Each hose is bagged individually and boxed. Longer hoses are coiled, bagged and boxed.

### Product tests

- Helium leak test ( $1 \times 10^{-5}$  std cm<sup>3</sup>/s)
- Additional options: he leak test  $1 \times 10^{-9}$  std cm<sup>3</sup>/s

## NATRIX

### End connections



Tube adapter



MFSM (male\*)




MFSF (female\*)

*\*Male and female adapter not available in 3/8"*

*Working pressure - temperature ratings may be limited by the end connections.*

CoreDux Product Range	Nominal Hose Size in (mm)	Tube Adapter	
		Stub thickness [in.(mm)]	Stub Outside Dia. [in. (mm)]
Natrix	1/4" DN006	0,035 (0,89)	0,25 (6,35)
Natrix	3/8" DN010	0,035 (0,89)	0,375 (9,53)
Natrix	1/2" DN012	0,049 (1,24)	0,5 (12,7)
Natrix	3/4" DN020	0,049 (1,24)	0,75 (19,05)
Natrix	1" DN025	0,065 (1,65)	1 (25,4)

### Ordering instructions



#### Options:

- Labelling requirements
- Ultra High purity
- Helium leak test (1x10<sup>-9</sup> cm3 std/s)
- Hydrostatic test
- Nitrogen pressure test